



Product Data Sheet

HT60-M3-CU High Temperature Circulator

[Print Data Sheet](#)

Product Image



Description

High Temperature Circulator for working temperatures up to 400 °C

JULABO high temperature circulators: The response to present requirements in the market. Peak performance, rapid heating and cooling, fast action in case of exotherm reactions - these are only few of the features of our high temperature circulators. The self-optimizing controller (ICC - Intelligent Cascade Control) ensures high temperature stability. The classic PID control parameters are available at the touch of a button for modification at any time. MULTI-DISPLAY (LED) and interactive LCD display offer convenient operation. The implemented heating automation, strong pump and controlled cooling produce rapid and precise results for temperature applications to +400 °C. The instruments are completely sealed. This prevents the release of oil fumes and results in long life time of the heat transfer liquid. Automatic air-purge allows easy filling. Electrical connections and the optional Profibus permit future-oriented automation technology. JULABO high temperature circulators are recommended for applications using jacketed reactors and autoclaves, distillation columns as well as laboratory, miniplant and process-scale applications.

Order Information

Model: HT60-M3-CU

Order no.: 9800066

Available mains power:
208V / 3 Ph. / 60Hz
230V / 3 Ph. / 60Hz

Similar Models

These models could also be interesting for you:

[HT60-M3-CU](#)

Advantages

- o Working temperature range up to 400 °C
- o Self-optimizing ICC temperature controller
- o Strong pumping capacity 18 l/min - 1.2 bar max
- o Automatic air-purge allows easy filling
- o Automated heat-up feature adjusts to external systems
- o Tap water cooling for temperatures from 40 to 400 °C and rapid cooling
- o Bright MULTI-DISPLAY (LED) with display resolution 0.01 °C
- o Backlit interactive 4-line LCD display
- o On-line communication via built-in RS232 interface
- o Analog setpoint/programmer input (0 to 20 mA / 0 to 10 V)
- o Integrated programmer stores up to 6 profiles (60 sections each)
- o Temperature recorder output (0 to 20 mA / 0 to 10 V)
- o Stand-by input for external emergency switch-off
- o Electronic level indication
- o ATC function for simple correction of temperature variations
- o ATC function allows use as testing instrument according to ISO 9000

Sales & Support:

+49 7823 51-190

Monday to Friday
7:30 am - 17:00 pm

JULABO Labortechnik GmbH
Eisenbahnstrasse 45
77960 Seelbach/Germany
Phone +49 7823 51-0
Fax +49 7823 2491
info@julabo.de
www.julabo.de

Technical changes reserved.
Pictures may differ from original.

Distributed by:



Carl Stuart Limited

ADVANCED APPLIED TECHNOLOGIES

Contact Us:

IrI Ph: 01 4523432
UK Ph: 08452 30 40 30
Web: www.carlstuart.com
Email: info@carlstuart.com

Technical Specifications

Working temperature range	40 ... 400 °C
Temperature control	PID+ICC
Temperature stability	±0.1 °C
Display	LED+LCD
Display resolution	0.01 °C
Integrated programmer	available
Heater capacity	6000 W
Pump capacity	Pressure: 1200 mbar Flow rate: 18 l/min
Digital interfaces	RS232, RS485, optional Profibus
External Pt100 sensor connection	available
Filling volume	2 Liters
Dimensions (W x L x H)	Thermostat: 43x23x58 / Regelelektronik: 25x25x18 cm
Weight	35 kg
Ambient temperature	5 ... 40 °C
Classification according to DIN 12876-1	3

Miscellaneous

Permissible cooling water pressure 4.5 bar max, pressure difference between IN and OUT: 2 to 4.5 bar